




Phonak Audéo L-RT (L90/L70/L50/L30/Trial)


S Receiver 2 cm³ coupler data

ANSI / ASA S3.22-2014
IEC 60118-0 : 2015

Output sound pressure level




Acoustic gain



Frequency range	<100 Hz - >8000 Hz			
Total harmonic distortion	500 Hz	800 Hz	1600 Hz	3200 Hz
	1.5%	2.0%	2.0%	1.0%
Expected operating time*	18	h		
Equivalent input noise level	19 dB SPL			


Induction coil sensitivity




M Receiver 2 cm³ coupler data

ANSI / ASA S3.22-2014
IEC 60118-0 : 2015

Output sound pressure level




Acoustic gain



Frequency range	<100 Hz - >8000 Hz			
Total harmonic distortion	500 Hz	800 Hz	1600 Hz	3200 Hz
	1.5%	2.0%	2.0%	1.0%
Expected operating time*	18	h		
Equivalent input noise level	19 dB SPL			

Induction coil sensitivity



General test information

- Specific measurement settings are used. RTS adjustment with volume control
- The device is operating in linear mode
- Low-level expansion is active
- All data obtained are measured with Phonak Target measurement settings

Warnings

- ⚠ This hearing instrument has an output sound pressure level that can exceed 132 dB SPL. Special care should be taken when fitting this instrument as there is a risk of impairing the residual hearing of the user.
- ⚠ Changes or modifications to the hearing aid that are not explicitly approved by the manufacturer are not permitted. Such changes may damage the ear or the hearing aid.

* Expected operating time of the rechargeable battery depends on active features, the use of wireless accessories, hearing loss, battery age and sound environment.



Sonova AG · Laubisrütistrasse 28
CH-8712 Stäfa · Switzerland
www.phonak.com

A Sonova brand




Phonak Audéo L-RT (L90/L70/L50/L30/Trial)


MAV Receiver 2 cm³ coupler data

ANSI / ASA S3.22-2014
IEC 60118-0 : 2015

Output sound pressure level




Acoustic gain



Frequency range	<100 Hz - >8000 Hz			
Total harmonic distortion	500 Hz	800 Hz	1600 Hz	3200 Hz
	1.5%	1.5%	1.0%	1.0%
Expected operating time*	18 h			
Equivalent input noise level	19 dB SPL			


Induction coil sensitivity




P Receiver 2 cm³ coupler data

ANSI / ASA S3.22-2014
IEC 60118-0 : 2015

Output sound pressure level




Acoustic gain



Frequency range	<100 Hz - 6300 Hz			
Total harmonic distortion	500 Hz	800 Hz	1600 Hz	3200 Hz
	1.0%	1.5%	1.0%	1.0%
Expected operating time*	18 h			
Equivalent input noise level	19 dB SPL			

Induction coil sensitivity




* Expected operating time of the rechargeable battery depends on active features, the use of wireless accessories, hearing loss, battery age and sound environment.

Phonak Audéo L-RT (L90/L70/L50/L30/Trial)


UP Receiver 2 cm³ coupler data

ANSI / ASA S3.22-2014
IEC 60118-0 : 2015

Output sound pressure level




Acoustic gain



Frequency range	<100 Hz - 6100 Hz			
Total harmonic distortion	500 Hz	800 Hz	1600 Hz	3200 Hz
	1.5%	1.5%	1.0%	1.0%
Expected operating time*	18	h		
Equivalent input noise level	19	dB SPL		

Induction coil sensitivity



* Expected operating time of the rechargeable battery depends on active features, the use of wireless accessories, hearing loss, battery age and sound environment.